


Stainless Steel Wetblast Cabinet

The Hydroblast stainless steel wetblast cabinets operate like a dry abrasive blasting machine but with the additional cleansing effect of water. This combination of water and media degreases and treats the metal surface simultaneously to provide a significantly "softer" matt finish. It is essentially a dust free process which is capable of descaling, decarbonising, and general cleaning to a surgical degree.



Stainless steel motorized workcar

HYDROBLAST 1010	Dimensions(mm)	1010(W)x1010(D)x2000(H)
HYDROBLAST 1212		1210(W)x1210(D)x2000(H)
HYDRABLAST 1515		1510(W)x1510(D)x2000(H)

Basic Model Features

- Grade 304 stainless steel construction
- Highly effective PU submersible pump for a more direct abrasive injection to the blast guns
- Durable polyurethane impeller & pump for long lasting usage
- Premium grade internal rubber lining
- Tungsten carbide nozzle

Optional

- Water heater
- Auto/Manual 100% stainless steel turntable workcar
- Settling tank
- Media concentration indicator
- Stainless steel rotating basket

